

STANDARD FLOOR PANELS



M335 Granite



H819 Alder



A0040 Oak

BERGVIK STANDARD FLOOR PANELS

Bergvik Laminate is a direct laminate with the laminate components pressed together with the floor substrate. Since the top and bottom layer is laminated together with the floor substrate there is no glue bond between the laminate and the substrate, this means that all forces onto the floor panel will be directed into the floor panel without affecting the laminate surface layer. The result is a very durable floor panel.

Bergvik laminate has antistatic properties (10^{10} - 10^{11} ohm), the limit for personal protection in electrical rooms is 50 kohm. The Bergvik panels are also environmentally friendly and fully recyclable.

Three standard decors of Bergvik laminate are; M335 Granite, H818 Alder and A0040 Oak. We also offer vinyl coverings from leading suppliers as an option. The floor panels can be delivered in two different qualities; V20 which is the standard quality in most spaces, or moist resistant quality V313. The core of our floor panels is a 1.5" highly density chipboard. The underside is coated with counter laminate.

To maximize the availability of the subfloor Bergvik can deliver floor panels in custom sizes. The standard sizes are 24" x 24", 31.5" x 24" and 16" x 24".

Benefits Bergvik laminate floor panels:

- Antistatic properties (10^{10} - 10^{11} ohm)
- Can be delivered in custom sizes 12" - 39" x 24"
- High mechanical strength
- Easy to handle thanks to its low weight (24" x 24" x 1.5" V20 22.7 lbs)
- Lightweight, durable and resistant to acids and chemicals
- Fire class Bfl-s1 according to 13501-1
- Load test according to EN 12825
- Direct laminated floorboard provides long life span and low cost of ownership
- Environmentally friendly and fully recyclable

